

OpEdge-8D v01.0.00 released

2022-10-15 - Christoph Strauss - Edge

New Features

- Docker Containers support for 3rd party application management
 - Configuration to deploy from Local UI and Belden Horizon portal
 - Support to download, manage and run docker containers
 - Container console access from local UI
 - Support for configuration of container networking
 - Bridge network
 - MACVLAN network
 - Host network
- Support for 3rd party virtual machines
 - Configuration from local UI
 - Upload and configure virtual machines ISO files
- Storage management of container images and VM images
- Container live stats update on local UI and Belden Horizon
- VM live stats update on local UI
- Porting of Docker engine and Qemu virtual machine engine
- Configurable DHCP Server
- Configurable DHCP client to get dynamic IP on ethernet ports
- Configure for WAN, LAN, NTP, Firewall, and NAT via Local UI
- Ethernet and Lan port configuration
 - Configuration on seven ethernet ports
 - Define LAN interfaces and membership assignment to ethernet ports
 - Support to configure ethernet ports in different

subnet

- Support of WAN on LAN feature
 - Any LAN interface can be defined as WAN
- Support for WAN network switchover
 - Two interfaces can be configured as alternate WAN networks.
 - Switches to alternate in case of failure
- Configurable NTP Server and Client
 - System time is synced from network automatically
 - Can be configured as server to sync time of the connected nodes
- Static Routes
 - Support to add routing entry manually
- Support to get system parameters via SNMP
- Capture, display and download System Logs from Local UI and Belden Horizon
- Configurable Firewall
 - Configurable Port Number
 - Port Forwarding
 - 5 Tuple
- Configurable Allowed IP List to control which source IP addresses are allowed to connect to the UI through the WAN interface.
- NAT (Network Address Translation)
 - Two types of NAT functionality is supported
 - IP Masquerading (Source NAT)
 - Port Forwarding (Destination NAT)
- Remapping an IP address into another by modifying network address information.
- File Relay
 - Enables simple and secure transfer of files across segmented networks
 - Incoming and outgoing file using FTP and SFTP protocol
 - Outgoing File Relay destination can be set to Belden Horizon
- Diagnostic feature
 - Ping utility on local UI
 - Remote packet capture support from Belden Horizon

- Account Management
 - Support to add 8 users (1 Admin and 7 Viewers) with different permission on local UI
 - Mandatory password change at first login
- Easy to use gateway activation on Belden Horizon
- VPN Tunnelling
 - Easy setup for Secure remote access (SRA) and Persistent data network (PDN) Tunnels
- Firmware upgrade support from local UI and Belden Horizon
- Configuration import and export feature to support customers to easily configure multiple gateways
- Reset to default configuration via factory reset feature
- Configure IP and factory reset from console CLI feature on serial port

Fixes & Changes

- N/A

Known Issues

- DHCP Server function on a newly configured LAN interface may, in rare occasions, fail to provide IP address to a device on that LAN.

Workaround: if a user sees this problem, a reboot on OpEdge-8D will resolve it.

- DHCP server may become unresponsive temporarily when DHCP Discover packet with protocol anomaly is received.

Workaround: DHCP Server function recovers after a few minutes (depending upon DHCP lease time) once protocol anomaly is removed. For faster recovery please reboot the OpEdge-8D device.

