

Configuration File Compare


- 2018-02-21 - Industrial HiVision

As of v6.0 IHV is able to monitor the configuration file of a device (Platform4, Platform5, EAGLE, BAT and GarrettCom).

Therefor the clear text configuration (script or xml) is stored in a property. The standard polling/status configuration can be used for comparing the current configuration to the reference config.


This lesson describes how to set a reference configuration and in case of configuration changes how you can display the differences.

Configuration File Properties



1. double click on the property Configuration File
2. press reload to download the current configuration from the device
3. open the status configuration

Configuration File - Status Config



In the status configuration dialog you can set the current value as reference value.

Change the configuration

Hirschmann Industrial HiView - 10.3.0.205 - Edit Mode

File Edit View Configuration Tools Help

Back Forward Up Home View Links Print Edit Mode Properties WWW Scan Network HiDiscovery Scan Preferences

Events: 0 2 1 187 Most Severe Recently: 2015-03-12 13:18:08 127.0.0.1:9000/Port 40/In Load Status: Impedance Error (In Load) -> 20.0, Current Value: 190.0

Selected VLAN:	All
10.3.0.135/Port 9-10 10.3.0.207	Agent
127.0.0.1:9000/Port 3-1227	Autocfg Adapter 1
127.0.0.1:9000/Port 3-1227	Autocfg Adapter 2
127.0.0.1:9000/Port 3-1227	Chassis MSP30-1804
127.0.0.1:9000/Port 3-1227	Configuration File SHA1 Version: 1.0
127.0.0.1:9000/Port 3-1227	Configuration Signature D68BCDC941NE230C...
127.0.0.1:9000/Port 3-1227	Configuration Status Not Saved
127.0.0.1:9000/Port 3-1227	Contact Hirschmann Automate...
127.0.0.1:9000/Port 3-1227	Interfaces
127.0.0.1:9000/Port 3-1227	Location
127.0.0.1:9000/Port 3-1227	Location Coordinates Hirschmann
127.0.0.1:9000/Port 3-1227	Module 1
127.0.0.1:9000/Port 3-1227	Module 2 MSP40-0711/0715/07...
127.0.0.1:9000/Port 3-1227	Module 3 MSP40-0711/0715/07...
127.0.0.1:9000/Port 3-1227	Module 4 MSP40-C1C3C3C15E...
127.0.0.1:9000/Port 3-1227	Module 5 MSP40-C1C3C3C15E...
10.3.0.3	Name MSP e65559P093C
127.0.0.1:9000/Port 3-1227	Order Code MSP30-1804RSC294...
127.0.0.1:9000/Port 3-1227	Power Supply 1
127.0.0.1:9000/Port 3-1227	Power Supply 2
127.0.0.1:9000/Port 3-1227	Product MSP
127.0.0.1:9000/Port 3-1227	Release
127.0.0.1:9000/Port 3-1227	QR Code 9420759994MSP30-...
127.0.0.1:9000/Port 3-1227	Role 1
127.0.0.1:9000/Port 3-1227	Role 2
127.0.0.1:9000/Port 3-1227	Security
127.0.0.1:9000/Port 3-1227	Serial Number 9420759990J0501590
127.0.0.1:9000/Port 3-1227	System Start 2015-02-27 11:47:55
127.0.0.1:9000/Port 3-1227	Temperature 43
10.3.0.205	Unit Hirschmann

10.3.0.205 - Location Properties

Property
Component: 10.3.0.205
Property: Location

Deploy
Name:
Icon: Realistic Abstract

Value
Current Value: Hirschmann PECE


Timestamp: Mar 12, 2015 12:14:43 PM
Value: Change After Trap
 Fill
Polling Interval: 1 Minutes
History: Record
Buffer Size: 100
Show Value in Tooltip of: Device

Status
Current Status: No Status
Status: Determine
 Forward Status Up

4

Change the device configuration e.g. the device location:

1. double click the property location
2. change the current value
3. press write



1. To set the current value as reference value on multiple devices navigate to the Properties tab.
2. Select the property 'Configuration File (Device)'
3. Highlight devices and select Multiconfig from the context menu (right click)
4. Go to Status Config and tick 'Set current to reference'