

## HiOS: HTML- How to use RSPAN

John M - 2024-02-16 - HiOS

This guide is designed to assist in the configuration of RSPAN on the layer 2 switches.


The configurations can be used in a 2 switch RSPAN network using SW1 and SW3

switch configurations. If the network is larger than 3 switches use the SW2

configuration in all the switches between the start and end switches.

### Network Topology

Switch 1 will be the switch that is doing the port mirroring. In this setup port 10 is being mirrored to port 6, port 6 is looped back to port 7 on VLAN 10, (it is important to turn RSTP off on ports 6 and 7 of switch 1), VLAN 10 is then forwarded across the uplinks to switch 3 port 11 where the mirrored packets can be monitored. **Note: the loop connection should be connected after switch 1 is fully configured.**



Switch Configuration:

### SW1

The VLANs will need to be configured as T for the uplink port and - for the looped ports in the comm vlan. Spanning tree needs to be disabled on the looped ports. Port mirroring needs to be enabled, the destination port selected, the source port enabled with the TX/RX selected for the type, and the RSPAN VLAN ID and the Destination VLAN ID need to be configured. See Screen shots below for reference.

VLAN Configuration														
<input type="checkbox"/> VLAN ID	Status	Creation time	Name	1/1	1/2	1/3	1/4	1/5	1/6	1/7	1/8	1/9	1/10	1/11
<input type="checkbox"/> 1	other	05s	default	U	U	U	T	U	-	-	U	U	U	U
<input type="checkbox"/> 10	permanent	09s		-	-	-	T	-	-	-	-	-	-	-

Spanning Tree Port					
CIST		Guards			
<input type="checkbox"/>	Port	STP active	Port state	Port role	Port path cost
<input type="checkbox"/>	1/1	<input checked="" type="checkbox"/>	disabled	disabled	0
<input type="checkbox"/>	1/2	<input checked="" type="checkbox"/>	disabled	disabled	0
<input type="checkbox"/>	1/3	<input checked="" type="checkbox"/>	disabled	disabled	0
<input type="checkbox"/>	1/4	<input checked="" type="checkbox"/>	forwarding	root	200,000
<input type="checkbox"/>	1/5	<input checked="" type="checkbox"/>	disabled	disabled	0
<input type="checkbox"/>	1/6	<input type="checkbox"/>	manualFwd	disabled	0
<input type="checkbox"/>	1/7	<input type="checkbox"/>	manualFwd	disabled	0
<input type="checkbox"/>	1/8	<input checked="" type="checkbox"/>	disabled	disabled	0
<input type="checkbox"/>	1/9	<input checked="" type="checkbox"/>	disabled	disabled	0
<input type="checkbox"/>	1/10	<input checked="" type="checkbox"/>	forwarding	designated	200,000
<input type="checkbox"/>	1/11	<input checked="" type="checkbox"/>	disabled	disabled	0

Port Mirroring				
Operation	Destination port		VLAN mirroring	RSPAN
<input checked="" type="radio"/> On <input type="radio"/> Off	Primary port	1/6	Source VLAN ID	0
	Allow management	<input type="checkbox"/>		VLAN ID 10 Destination VLAN ID 10
<input type="checkbox"/>	Source port	Enabled	Type	
<input type="checkbox"/>	1/1	<input type="checkbox"/>	none	
<input type="checkbox"/>	1/2	<input type="checkbox"/>	none	
<input type="checkbox"/>	1/3	<input type="checkbox"/>	none	
<input type="checkbox"/>	1/4	<input type="checkbox"/>	none	
<input type="checkbox"/>	1/5	<input type="checkbox"/>	none	
<input type="checkbox"/>	1/6	<input type="checkbox"/>	none	
<input type="checkbox"/>	1/7	<input type="checkbox"/>	none	
<input type="checkbox"/>	1/8	<input type="checkbox"/>	none	
<input type="checkbox"/>	1/9	<input type="checkbox"/>	none	
<input type="checkbox"/>	1/10	<input checked="" type="checkbox"/>	txrx	
<input type="checkbox"/>	1/11	<input type="checkbox"/>	none	

## SW2

The VLANs will need to be configured as T for the uplink ports. In the Port mirroring tab RSPAN VLAN ID needs to be configured. See Screen shots below for reference

VLAN Configuration															
VLAN ID	Status	Creation time	Name	1/1	1/2	1/3	1/4	1/5	1/6	1/7	1/8	1/9	1/10	1/11	
1	other	05s	default	U	U	U	T	T	U	U	U	U	U	U	
10	permanent	09s		-	-	-	-	T	-	-	-	-	-	-	

Port Mirroring			
Operation	Destination port	VLAN mirroring	RSPAN
<input type="radio"/> On <input checked="" type="radio"/> Off	Primary port: <input type="text" value="-"/> Allow management: <input type="checkbox"/>	Source VLAN ID: <input type="text" value="0"/>	Source VLAN ID: <input type="text" value="0"/> VLAN ID: <input type="text" value="10"/> Destination VLAN ID: <input type="text" value="0"/>

<input type="checkbox"/> Source port	Enabled	Type
<input type="checkbox"/> 1/1	<input type="checkbox"/>	none
<input type="checkbox"/> 1/2	<input type="checkbox"/>	none
<input type="checkbox"/> 1/3	<input type="checkbox"/>	none
<input type="checkbox"/> 1/4	<input type="checkbox"/>	none
<input type="checkbox"/> 1/5	<input type="checkbox"/>	none
<input type="checkbox"/> 1/6	<input type="checkbox"/>	none
<input type="checkbox"/> 1/7	<input type="checkbox"/>	none
<input type="checkbox"/> 1/8	<input type="checkbox"/>	none
<input type="checkbox"/> 1/9	<input type="checkbox"/>	none
<input type="checkbox"/> 1/10	<input type="checkbox"/>	none
<input type="checkbox"/> 1/11	<input type="checkbox"/>	none

## SW3

Finally use the screen shots to as a guide for switch 3 configuration of VLANs and port mirroring/RSPAN The VLANs will need to be configured as T for the uplink port and - for the destination port in the comm vlan. Port mirroring needs to be enabled, the destination port selected, and the RSPAN Source VLAN ID and the VLAN ID need to be configured. See Screen shots below for reference.

VLAN Configuration															
VLAN ID	Status	Creation time	Name	1/1	1/2	1/3	1/4	1/5	1/6	1/7	1/8	1/9	1/10	1/11	
1	other	05s	default	U	U	U	T	U	U	U	U	U	U	-	
10	permanent	09s		-	-	-	-	-	-	-	-	-	-	-	

Port Mirroring			
Operation	Destination port	VLAN mirroring	RSPAN
<input checked="" type="radio"/> On <input type="radio"/> Off	Primary port: <input type="text" value="1/11"/> Allow management: <input type="checkbox"/>	Source VLAN ID: <input type="text" value="0"/>	Source VLAN ID: <input type="text" value="10"/> VLAN ID: <input type="text" value="10"/> Destination VLAN ID: <input type="text" value="0"/>

<input type="checkbox"/> Source port	Enabled	Type
<input type="checkbox"/> 1/1	<input type="checkbox"/>	none
<input type="checkbox"/> 1/2	<input type="checkbox"/>	none
<input type="checkbox"/> 1/3	<input type="checkbox"/>	none
<input type="checkbox"/> 1/4	<input type="checkbox"/>	none
<input type="checkbox"/> 1/5	<input type="checkbox"/>	none
<input type="checkbox"/> 1/6	<input type="checkbox"/>	none
<input type="checkbox"/> 1/7	<input type="checkbox"/>	none
<input type="checkbox"/> 1/8	<input type="checkbox"/>	none
<input type="checkbox"/> 1/9	<input type="checkbox"/>	none
<input type="checkbox"/> 1/10	<input type="checkbox"/>	none
<input type="checkbox"/> 1/11	<input type="checkbox"/>	none

